



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **WC0J Orn Twist-On Wire Conn 700PC Jar** *Nsi Industries*

Catalog Number	WC0J
Manufacturer	Nsi Industries
Description	The Easy-Twist WC-O-J 700-Count Jar Of Standard-Style Orange Wire Connectors Are Designed For Use On Copper Wires In The 22-14 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Ribbed Texture Makes Them Easy To Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to Connect
Weight per unit	2.4 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### **Features**

Material	Thermoplastic
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	COPPER

### **Material, Color, and Finish**

Color	Orange
Finish	Thermoplastic

### **Dimensions and Weight**

Depth	.197
Height	.866



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	ORN TWIST-ON WIRE CONN 700PC JAR
extra long description	NSI WC-O-J Easy-Twist Orange - Lg J
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in
Long Description	The Easy-Twist WC-O-J 700-Count Jar of Standard-Style Orange Wire Connectors are designed for use on copper wires in the 22-14 AWG size range. Theyâ€™re made of flame-retardant thermoplastic rated for a maximum temperature of 105Ëš Celsius (221Ëš Fahrenheit). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you need to connect
Product Type	Easy-Twist Orange - LG Jar
Special Features	Standard Orange Wire Connector - 700 Pcs Jar

## Manufacturer Information

Brand	NSi
GTIN	00662381140258
Manufacturers Part Number	WC-O-J
UPC	662381140258

## Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Standard Wire Connectors

## Packaging

Carton	1
Package	700
Weight Per jar	2.37

## Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C