



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WC0J Orn Twist-On Wire Conn 700PC Jar

Nsi Industries

| | |
|------------------|--|
| Catalog Number | WC0J |
| Manufacturer | Nsi Industries |
| Description | The Easy-Twist WC-O-J 700-Count Jar Of Standard-Style Orange Wire Connectors Are Designed For Use On Copper Wires In The 22-14 Awg Size Range. They're Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105°C (221°F Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Ribbed Texture Makes Them Easy To Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to Connect |
| Weight per unit | 2.4 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|---------------|
| Material | Thermoplastic |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Type | COPPER |

Material, Color, and Finish

| | |
|--------|---------------|
| Color | Orange |
| Finish | Thermoplastic |

Dimensions and Weight

| | |
|--------|------|
| Depth | .197 |
| Height | .866 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | ORN TWIST-ON WIRE CONN 700PC JAR |
| extra long description | NSI WC-O-J Easy-Twist Orange - Lg J |
| Features | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in |
| Long Description | The Easy-Twist WC-O-J 700-Count Jar of Standard-Style Orange Wire Connectors are designed for use on copper wires in the 22-14 AWG size range. They are made of flame-retardant thermoplastic rated for a maximum temperature of 105°C (221°F). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you need to connect |
| Product Type | Easy-Twist Orange - LG Jar |
| Special Features | Standard Orange Wire Connector - 700 Pcs Jar |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381140258 |
| Manufacturers Part Number | WC-O-J |
| UPC | 662381140258 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | WIRE NUTS |
| Type | Standard Wire Connectors |

Packaging

| | |
|----------------|------|
| Carton | 1 |
| Package | 700 |
| Weight Per jar | 2.37 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------|
| Application | Splicing Wire |
| environmental conditions | 105 C |
| standard | UL 486C |