



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WF4LED30K40K50K0 4" 10W Led Wafer 3K/4K/5K Bronze 90cri

*Lithonia Lighting - Acuity*

Catalog Number	WF4LED30K40K50K0
Manufacturer	Lithonia Lighting - Acuity
Description	Lith WF4 Led 30K40K50K 90CRI Orb M6
Weight per unit	1.6 (lbs/each)
Product Category	Led Recessed Architectural & S

### Features

average life	35,000
dimnable	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
Material	Aluminum
Maximum Operating Temperature	25
media	Yes
pallet quantity	324
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	11

### Material, Color, and Finish

Color	Bronze
color rendering index (cri)	90
color temperature	Variable
Finish	Oil Rubbed
Lens Color	WHITE
Lens Material	Polycarbonate

### Dimensions and Weight

Height	1.1
Length	4.7
Width	4.7

### Descriptions

Construction	Canless,New Construction,Remodel
Description	4" 10W LED WAFER 3K/4K/5K BRONZE 90CRI
Long Description	LITH WF4 LED 30K40K50K 90CRI ORB M6
Product Type	Downlight



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848253830
Manufacturers Part Number	WF4 LED 30K40K50K 90CRI ORB M6
UPC	191848253830

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

## Trade Size

aperture size	4 in
---------------	------

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Package	6
Weight	1
Weight Per each	1.6

## Uses, Certifications, and Standards

Application	Automotive & Parking,Education,Government,Healthcare,Hospitality,House of Worship,Manufacturing,Power & Gas,Residential,Retail,Sports and Recreation,Transportation,Warehouses
environmental conditions	Indoor
Mounting	Recessed
standard	CSACA Title 24,JA8