



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## **WF6AL020SWW590CR 6" Led Wafer 27K/3K/35K/4K/5K 800/1050/1300LM**

*Lithonia Lighting - Acuity*



Catalog Number	WF6AL020SWW590CR
Manufacturer	Lithonia Lighting - Acuity
Description	The 6IN Canless Wafer Downlight Has An Innovative, Slim Design That Installs Quickly and Easily Into As Little As 3IN Of Plenum Space Allowing For It to Fit Into Ceiling Spaces Where Most Traditional Recessed Housings Do Not. Wafers Install Directly Into Dry Wall Eliminating The Need For Recessed Housings. Once Installed, Our Wafer Provides An All-In-One Design Featuring Switchable White Color Temperature and Adjustable Lumen Output Technology. This Technology Gives The Ultimate In Flexibility, Providing Y
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

### **Features**

average life	50,000
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1050 LM,1300 LM,800 LM
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	3
Wattage	16

### **Material, Color, and Finish**

Color	White
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,4000 ,5000 ,Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate
Style	CONTEMPORARY



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Dimensions and Weight

Height	1.25
Length	6.69
Width	6.69

## Descriptions

Construction	Canless,New Construction,Remodel
Description	6" LED WAFER 27K/3K/35K/4K/5K 800/1050/1300LM
extra long description	LITH WF6 ALO20 SWW5 90CRI CP6 MW M2
Features	Contractor Select
Long Description	The 6in Canless Wafer Downlight has an innovative, slim design that installs quickly and easily into as little as 3in of plenum space allowing for it to fit into ceiling spaces where most traditional recessed housings do not. Wafers install directly into dry wall eliminating the need for recessed housings. Once installed, our Wafer provides an all-in-one design featuring switchable white color temperature and adjustable lumen output technology. This technology gives the ultimate in flexibility, providing y
Product Type	Downlight

## Manufacturer Information

Brand	Lithonia Lighting - Acuity
GTIN	00197589041248
Manufacturers Part Number	WF6 ALO20 SWW5 90CRI MW M6
UPC	197589041248

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

## Trade Size

aperture size	6 in
---------------	------

## Packaging

Carton	1
Package	6
Weight	1.23
Weight Per each	1.36

## Uses, Certifications, and Standards

Application	Decorative,Hospitality,Residential,Retail
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8