



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF6LED30K40K50K0 *Discontinued* 6" Led Wafer 30K40K50K BRZ *Lithonia Lighting - Acuity*

Catalog Number	WF6LED30K40K50K0
Manufacturer	Lithonia Lighting - Acuity
Description	Lith WF6 Led 30K40K50K 90CRI Orb M6
Weight per unit	2.2 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

dimensions	1100 LM
dimmmable	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1100 LM
Material	Aluminum
Maximum Operating Temperature	25
media	Yes
pallet quantity	180
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	14

Material, Color, and Finish

Color	Bronze
color rendering index (cri)	90
color temperature	Variable
Finish	Oil Rubbed
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	1.1
Length	6.7
Width	6.7

Descriptions

Construction	Canless,New Construction,Remodel
Description	*DISCONTINUED* 6" LED WAFER 30K40K50K BRZ
Long Description	LITH WF6 LED 30K40K50K 90CRI ORB M6
Product Type	Downlight



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848254257
Manufacturers Part Number	WF6 LED 30K40K50K 90CRI ORB M6
UPC	191848254257

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

Trade Size

aperture size	6 in
---------------	------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	1.6
Weight Per each	2.2

Uses, Certifications, and Standards

Application	Education,Hospitality,House of Worship,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSACA Title 24,ENERGY STAR,JA8