



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF6SWW590CRIMWM6 6" 13W Led Wafer 27K/3K/35K/4K/5K 970LM

Lithonia Lighting - Acuity

| | |
|------------------|---|
| Catalog Number | WF6SWW590CRIMWM6 |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The 6-Inch Juno® Wafer™ Led Downlights With Switchable White Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment, While Eliminating The Need For Recessed Housings. The Innovative Switchable White Feature Incorporates A Switch On Each Fixture For Simple Color Temperature Adjustment. Too Warm or Too Cool? Simply Toggle The Integrated Switch to Your Desired Setting (3000K Factory Default) and You Are Done! Whatever Your Application, Luminaires With Swi |
| Weight per unit | 1.8 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-------------------------------|-----------------|
| average life | 50,000 |
| dimensions | 6.7 x 6.7 x 1.1 |
| dimnable | Yes |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Dynamic |
| lumens | 950 lm |
| Material | Aluminum |
| Maximum Operating Temperature | 25 |
| Number of Lamps | 1 |
| Power Source | Hardwired |
| Shape | Round |
| Voltage Rating | 120 |
| Warranty | 3 |
| Wattage | 13 |

Material, Color, and Finish

| | |
|-----------------------------|--|
| Color | White |
| color rendering index (cri) | 90 |
| color temperature | 2700 ,3000 ,3500 ,4000 ,5000 ,Variable |
| Finish | Matte |
| Lens Color | WHITE |
| Lens Material | Polycarbonate |
| Style | CONTEMPORARY |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

| | |
|--------|------|
| Height | 1.1 |
| Length | 76.7 |
| Width | 76.7 |

Descriptions

| | |
|------------------------|---|
| Construction | Canless,New Construction,Remodel |
| Description | 6" 13W LED WAFER 27K/3K/35K/4K/5K 970LM |
| extra long description | LITH WF6 SWW5 90CRI MW M6 6IN wafer |
| Features | Contractor Select |
| Long Description | The 6-inch Juno® Wafer™ LED Downlights with Switchable White provides high-quality light output and efficiency and features a switch for easy color temperature adjustment, while eliminating the need for recessed housings. The innovative Switchable White feature incorporates a switch on each fixture for simple color temperature adjustment. Too warm or too cool? Simply toggle the integrated switch to your desired setting (3000K factory default) and you are done! Whatever your application, luminaires with Swi |
| Product Type | Downlight |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | JUNO |
| GTIN | 00194994243731 |
| Manufacturers Part Number | WF6 SWW5 90CRI MW M6 |
| UPC | 194994243731 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | Downlight |

Trade Size

| | |
|---------------|------|
| aperture size | 6 in |
|---------------|------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 6 |
| Weight | 1.5 |
| Weight Per each | 1.8 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Decorative,Hospitality,Residential,Retail |
| environmental conditions | Indoor,Outdoor |
| Mounting | Recessed |
| standard | CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8 |