



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF8SWW590CRIMWM6 8" 20W Led Wafer 27K/3K/35K/4K/5K WHT 120V *Lithonia Lighting - Acuity*

Catalog Number	WF8SWW590CRIMWM6
Manufacturer	Lithonia Lighting - Acuity
Description	The Wafer Led Downlights With Switchable White Technology Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment, While Eliminating The Need For Recessed Housings.
Weight per unit	2.3 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	1600 LM
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1600 LM
Material	Aluminum
Shape	Round
Voltage Rating	120
Warranty	3
Wattage	19.1

Material, Color, and Finish

Color	White
color temperature	2700 ,3000 ,3500 ,4000 ,5000 ,Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	1.1
Length	8.9
Width	8.9



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Canless,New Construction,Remodel
Description	8" 20W LED WAFER 27K/3K/35K/4K/5K WHT 120V
extra long description	LITH WF8 SWW5 90CRI MW M6 8IN wafer
Long Description	The Wafer LED Downlights with Switchable White technology provides high-quality light output and efficiency and features a switch for easy color temperature adjustment, while eliminating the need for recessed housings.
Product Type	Trim

Manufacturer Information

Brand	JUNO
GTIN	00194994243915
Manufacturers Part Number	WF8 SWW5 90CRI MW M6
UPC	194994243915

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

Trade Size

aperture size	8 IN
---------------	------

Packaging

Carton	1
Package	6
Weight Per each	2.3

Uses, Certifications, and Standards

Application	Education,Healthcare,Hospitality,House of Worship,Residential,Retail,Sports and Recreation
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSACA Title 24,ENERGY STAR,JA8