

SURE-LITES®

ORDERING INFORMATION

Cat. No.	Length	Height	Depth	For use with
VS1	21" (533mm)	11" (279mm)	10" (254mm)	AA, CAX, CC, CCX (AC only or Self-Powered), CHX (AC only), CU, LM, P4C, PLX (AC only), R/G/CX/OF, CX, LPX (without heads), ST Series; Remote Heads
VS1WP	21" (533mm)	11" (279mm)	10" (254mm)	AA, CAX, CC, CCX (AC only or Self-Powered), CHX (AC only), CU, LM, P4C, PLX (AC only), R/G/CX/OF, CX, LPX (without heads), ST Series; Remote Heads
VS2	21" (533mm)	19" (483mm)	11" (279mm)	CCX (with Heads), CHX (Self-Powered), UN/UNH (Self-Powered or with Heads), HR, NCB (except NCB12225), PLX (Self-Powered or with Heads), LPX (with heads), UMB, XR Series, CC7, CC8
VS2WP	21" (533mm)	19" (483mm)	11" (279mm)	CCX (with Heads), CHX (Self-Powered), UN/UNH (Self-Powered or with Heads), HR, NCB (except NCB12225), PLX (Self-Powered or with Heads), LPX (with heads), UMB, XR Series CC7, CC8

DESCRIPTION

- Made of durable, high-impact, UV-resistant clear polycarbonate material
 - Self-adhesive closed-cell neoprene gaskets provided with "WP" weather resistant versions
 - "WP" weather resistant versions are provided with gasketed breather vent
- UL 924 Rain Test (SD4.6), UL 924 Water Shield Impact Test (SD4.10)



POLYCARBONATE VANDAL SHIELD/WEATHER SHIELD

ORDERING INFORMATION

Catalog No.	Length	Height	Depth	For use with
WG1	18" (457mm)	15" (381mm)	6" (152mm)	CC, LM1, AA, XR, CU2, CAX (Incandescent/Fluorescent, Self-Powered, Surface Mount) Series
WG2	18" (457mm)	15" (381mm)	10" (254mm)	PLX (with heads), UNH (with heads), CCX (with heads) & CHX (with heads)
WG3	23" (584mm)	20" (508mm)	12" (305mm)	HR180, HR12170, HR12210, HR12360, NCB45, NCB90, NCB110, NCB1290, NCB12180 Series, CC7, CC8
WG4	32" (812mm)	21" (533mm)	12" (305mm)	NCB12225 Series
WG5	16" (406mm)	16" (406mm)	14" (356mm)	SLC1, CFR1 Series
WG6	26" (660mm)	16" (406mm)	14" (356mm)	SLC2, CFR2 Series
WG7	16" (406mm)	16" (406mm)	9" (229mm)	P4C, RLM, RD, R4C, HR87, HR117, HR12117, UMB, UMX Series
WG8	8" (203mm)	8" (203mm)	8" (203mm)	Single Head Remotes
WG9	16" (406mm)	8" (203mm)	8" (203mm)	Double Head Remotes, ST1
WG10	13 3/4" (349mm)	13 3/8" (340mm)	4 3/8" (111mm)	R, G, CX, UN, UNH, PLX, CCX, SLX, LPX/LPXH, INCX, TRX, CAX (Incandescent/Fluorescent, AC), CAX-LED Series (Surface Mount Only—CU2), CHX
WGS11	13 5/8" (346mm)	16 3/4" (425mm)	4" (102mm)	R, G, CX, UN, UNH, PLX, CCX, SLX, LPX/LPXH, CAX, INCX, TRX Series (End or Ceiling Mount Only), CHX
WG12	27 1/2" (698mm)	14" (356mm)	8" (203mm)	GC Series, LPX (with heads-wall)
WG17	27 1/2" (698mm)	12" (305mm)	14 1/2" (368mm)	GC Series, LPX (with heads-ceiling or wall)
WG19	21" (533mm)	15" (381mm)	6" (152mm)	CU1 Series

DESCRIPTION

Wire Guards

- All metal wire guard for exits or emergency units
- .177" (5mm) diameter 7 gauge steel round wire
- Non reflective zinc plated finish
- Hinged sides hook in place (except WGS11 which is not hinged)
- Screw eyes provided for mounting



WIRE GUARDS

ORDERING INFORMATION

Pendant Kits			
Catalog No.	Finish	Length	For use with
PK18WH	White	18"	R/G/CX/OF/SLX/UN/UNH/PLX Series Steel Exits
PK18BK	Black	18"	R/G/CX/OF/SLX/UN/UNH/PLX Series Steel Exits
CCX18PKWH	White	18"	CCX/LPX Series Exits
CCX18PKBK	Black	18"	CCX/LPX Series Exits
CAX18PKWH	White	18"	CAX Series Exits with incandescent or compact fluorescent lamps which are 120/277VAC Only or are self-powered emergency; all CAX Series Exits with LED lamps, CX6 & CX7 Series, HR Series and CU2 Series
CAX18PKBK	Black	18"	
CAX18PKBZ	Bronze	18"	

DESCRIPTION

Pendant Kit

- Pendant Kit for pendant mounting of exits
- No electrical components
- Includes canopy, mounting hardware, threaded stem and attachment bracket
- CAX Series Pendant Kit may require CAX Series Splice Box



PENDANT KITS

Note: Contact Cooper Lighting Representative for Custom Lengths

DESCRIPTION

The Metrolite ML Series is the right choice for installations where aesthetics are a priority. With its white finish and sculptured compact design the product blends in with the surroundings. Matching remotes are available to insure a consistent appearance. The pleasing look is accompanied by a feature rich design that provides fully adjustable heads with high efficiency halogen lamps making it easy to direct ample light to the required areas. Each unit employs a quick mount universal back with hinged access for hassle free installation.

DIMENSIONS



ELECTRICAL RATINGS

Rated Wattage to 87 1/2 % of Rated D.C. Voltage

Model	DC Voltage	1 1/2 Hours	Remote Wattage Available
ML1	6	25	0
ML2	6	50	26
ML3	12	50	26
ML4NC	6	14	0
ML5NC	12	28	0

Lamp Information

Type	Wattage	Number
Bi-Pin Halogen	12W ea	029-66
Bi-Pin Halogen	12W ea	029-66
Bi-Pin Halogen	12W ea	029-45
Bi-Pin Halogen	6W ea	029-12
Bi-Pin Halogen	12W ea	029-45

ORDERING INFORMATION

SAMPLE NUMBER: ML1

Model Number	Options (add as suffix)	Accessories
ML1	V = Voltmeter	(Order separately)
ML2	TDM= Time Delay Monitor	VS1 = Polycarbonate Vandal Shield
ML3	Alternate Lamps ²	WG12 = Wire Guard
ML4NC ¹		
ML5NC ¹		

ENERGY DATA

Input Current (Max.)

ML1, ML2, ML3

120V = .3A

277V = .1A

ML4NC, ML5NC

120V = .085A

277V = .035A

ML SERIES
METROLITEMETROLITE
EMERGENCY LIGHT

- > Dual-voltage input 120/277VAC, 60Hz
- > Injection-Molded, High-Impact, Thermoplastic Housing, Rated UL 94-5VA, Designer-White Textured Finish, Integral Mounting Plate
- > Glare Free Lens, Fully Adjustable, Halogen Lamps
- > Sealed Lead Calcium or Nickel Cadmium Battery Maintenance Free, Long Life, Full Recharge time, 24 Hours (max.)
- > Line-Latching, Low-Voltage Disconnect, Test Switch, AC Power Indicator, Brownout Circuit
- > Red LED High Charge Indicator, Amber LED AC Power Indicator
- > UL 924, Life Safety NFPA 101, NEC/OSHA, Most State and Local Codes

¹NC = Nickel Cadmium Battery. ²Consult your Cooper Lighting Representative.