



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WMB21 Nsi WMB-21 Wire Marker Book(1X) *Nsi Industries*

| | |
|------------------|-----------------------------|
| Catalog Number | WMB21 |
| Manufacturer | Nsi Industries |
| Description | Wire Marker Book(1X3 Blank) |
| Weight per unit | 0.0900 (lbs/each) |
| Product Category | Markers & Marking Tapes |

Features

| | |
|-----------------|-----------------------------------|
| Legend | 1 x 3 Blank (1 x 1 Write on Area) |
| Material | Vinyl Impregnated Cloth |
| Number of Pages | 10 |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|------------------|-------|
| Background Color | NSI |
| Legend Color | Black |

Dimensions and Weight

| | |
|------|-----------------|
| Size | H=6.00 - W=3.25 |
|------|-----------------|

Descriptions

| | |
|------------------------|--|
| Description | NSI WMB-21 WIRE MARKER BOOK(1X |
| extra long description | NSI WMB-21 Wire Marker Book 1X3 Bla |
| Features | Wire Marker Book(1X3 Blank) |
| Long Description | Wire Marker Book(1X3 Blank) |
| Product Type | Wire Marker Book 1X3 Blank |
| Special Features | Made with Vinyl Impregnated Cloth, strong adhesive ensures marking will last |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381090171 |
| Manufacturers Part Number | WMB-21 |
| UPC | 662381090171 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
| Type | Wire Marker Books |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.09 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Wire Identification

Temperature Rating

-40 F to 250 F