



## 1-GANG, 1-PORT OVERSIZED WALL PLATE, WHITE

WP3301-WH | [On-Q](#)

### FEATURES & BENEFITS

Our durable Oversized Wall Plates are available in White and Light Almond and come in your choice of blank, 1, 2, 3, 4, or 6 openings.



### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Product Series: Classic  
Type: Oversized Keystone Wallplate

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990  
CSA Standard: Yes  
UL Listing No: ANSI/UL 1863  
UL Standard: Yes  
UN SPSC: 39121704

#### CONSTRUCTION INFORMATION

Installation Location: In-Wall

#### DIMENSIONS

Depth (Metric): 6 mm  
Depth (US): 0.22"  
Height (Metric): 12.4 cm  
Height (US): 4.87"

Width (Metric): 7.9 cm

Width (US): 3.11 in

#### TECHNICAL INFORMATION

Material: High Impact Flame Retardant Plastic

Receptacle Type: Keystone Cutout

Number Of Receptacles: 1



## 1-GANG, 1-PORT OVERSIZED WALL PLATE, WHITE

WP3301-WH | [On-Q](#)

### FEATURES & BENEFITS

Our durable Oversized Wall Plates are available in White and Light Almond and come in your choice of blank, 1, 2, 3, 4, or 6 openings.



### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Product Series: Classic  
Type: Oversized Keystone Wallplate

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990  
CSA Standard: Yes  
UL Listing No: ANSI/UL 1863  
UL Standard: Yes  
UN SPSC: 39121704

#### CONSTRUCTION INFORMATION

Installation Location: In-Wall

#### DIMENSIONS

Depth (Metric): 6 mm  
Depth (US): 0.22"  
Height (Metric): 12.4 cm  
Height (US): 4.87"

Width (Metric): 7.9 cm

Width (US): 3.11 in

#### TECHNICAL INFORMATION

Material: High Impact Flame Retardant Plastic

Receptacle Type: Keystone Cutout

Number Of Receptacles: 1