Pass and Seymour
Weatherproof Two Gang Box, Gray
Part No. WPBD452



Weatherproof 2 Gang Deep Box, 5 Hole 1 37 Cu.In. with Threaded Holes,Gray (2 Holes Each End, 1 Hole in Back)

Features & Benefits

- Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.
- 4 closure plugs and mounting lugs furnished with all boxes.
- UL listed for wet and/or damp locations with appropriate cover.
- Designed for both interior and exterior applications.
- Will accept standard three-gang weatherproof covers.
- Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.
- Heavy die-cast aluminum.
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007116052	Country Of Origin	India
Material	Die-Cast Aluminum	Features	Corrosion Resistant, Weatherproof
Number of Knockouts	3	Application Sector	Commercial, Residential
Standard	UL listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof		

Dimensions

Product Width US	4.5 in	Product Depth US	2.72 in
Product Height US	4.5 in	Cubic Capacity	37 in^3

Box Depth	Deep

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695

Technical Information

Number of Gangs	2	Size of Threaded Openings	1 in
Indoor/Outdoor	Both	Cable Entry	Back, Bottom, Top
Box Shape	Square	Mounting Type	Screw Mount