



COMMERCIAL PASSIVE INFRARED (PIR) WALL SWITCH SENSOR, LIGHT ALMOND

WSP250LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Passive Infrared Wall Switch Sensor, 1050 sq.ft. coverage, 120 VAC 60 Hz/277 VAC 60Hz, Light Almond



- 180-degree PIR Coverage
- Built in light level sensor
- LED detection indicator
- Dual-voltage model; 120/277 VAC
- 1-inch deep back body and flying leads for easy installation
- Time delay adjustment from 30 seconds to 30 minutes
- Adjustable unit sensitivity (light sensing) from 20% to 100%
- Supplied with matching TP26 nylon wall plate
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Type: Occupancy
Features: Passive Infrared
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

TECHNICAL INFORMATION

Mounting: Wall
Volts: 120/277VAC
Watts: 800/1200

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No



COMMERCIAL PASSIVE INFRARED (PIR) WALL SWITCH SENSOR, LIGHT ALMOND

WSP250LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Passive Infrared Wall Switch Sensor, 1050 sq.ft. coverage, 120 VAC 60 Hz/277 VAC 60Hz, Light Almond



- 180-degree PIR Coverage
- Built in light level sensor
- LED detection indicator
- Dual-voltage model; 120/277 VAC
- 1-inch deep back body and flying leads for easy installation
- Time delay adjustment from 30 seconds to 30 minutes
- Adjustable unit sensitivity (light sensing) from 20% to 100%
- Supplied with matching TP26 nylon wall plate
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Type: Occupancy
Features: Passive Infrared
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

TECHNICAL INFORMATION

Mounting: Wall
Volts: 120/277VAC
Watts: 800/1200

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No