



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WT3B Wiretwist Wire Connector, WT3 Orange, 500/Bag

Ideal

Catalog Number	WT3B
Manufacturer	Ideal
Description	Buchanan, Wire Connector, Wiretwist, Conductor Range: 22 - 14 Awg, 2/18 Awg Min, 2/14 Awg Max, Number Of Conductors: 3 to 5, Material: Flame-Retardant Polypropelene, Color: Orange, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT3
Weight per unit	0.0020 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Orange
-------	--------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT3 ORANGE, 500/BAG
extra long description	IDEAL WT3-B WIRE-TWIST CONN.,ORANGE
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing
Long Description	Buchanan, Wire Connector, WireTwist, Conductor Range: 22 - 14 AWG, 2/18 AWG Min, 2/14 AWG MAX, Number Of Conductors: 3 to 5, Material: Flame-retardant Polypropelene, Color: Orange, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT3
Product Type	Wire-Twist Conn., Orange, Bag500
Special Features	1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip;Model Number: WT3;Ribbed Cap Provides Positive Grip For Fast, Easy Installation;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F);UL 486C Listed And CSA 22.2 #188 Certified

Manufacturer Information

Brand	Buchanan
GTIN	00781789610054
Manufacturers Part Number	WT3-B
UPC	781789610054

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

Availability

minimum qty	500
-------------	-----

Packaging

Carton	500
Package	10000
Weight Per each	0.002



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS