



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WT41B Wingtwist Wire Connector, WT41 Tan, 500/Bag

Ideal

Catalog Number	WT41B
Manufacturer	Ideal
Description	Buchanan, Wire Connector, Wingtwist, Conductor Range: 22 - 10 Awg, 2/20 Awg Min, 3/10 Solid Awg Max, Number Of Conductors: 1 to 6, Material: Flame-Retardant Polypropelene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT41
Weight per unit	0.0040 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Tan
-------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WINGTWIST WIRE CONNECTOR, WT41 TAN, 500/BAG
extra long description	IDEAL WT41-B WINGTWIST WT41 TAN, 50
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value. The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections. With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric protection.
Long Description	Buchanan, Wire Connector, WingTwist, Conductor Range: 22 - 10 AWG, 2/20 AWG Min, 3/10 Solid AWG MAX, Number Of Conductors: 1 to 6, Material: Flame-retardant Polypropylene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT41
Product Type	Wingtwist WT41 Tan, 500 Bag
Special Features	1,000V Maximum In Fixtures And Signs; Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection; Features: Five Color-Coded Models Cover Common Construction Wire Ranges; Fixed, Square-Wire Spring Threads Itself Creating Secure Pressure Grip; Green Model Designed For Ground Connections; Model Number: WT41; UL 486C Listed (WGR UL 467 Listed) And CSA C22.2 #188 Certified; Unique Contoured Wing Design Acts As Built-In Wrench Providing Maximum Torque With Minimum Effort

Manufacturer Information

Brand	Ideal
GTIN	00781789967677
Manufacturers Part Number	WT41-B
UPC	781789967677

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

Availability

minimum qty	500
-------------	-----

Packaging

Carton	500
Package	5000
Weight Per each	0.004



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS