



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WT4B Wiretwist Wire Connector, WT4 Yellow, 500/Bag

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | WT4B  |
| Manufacturer     | Ideal   |
| Description      | Buchanan, Wire Connector, Wiretwist, Conductor Range: 18 - 10 Awg, 3/18 Awg Min, 4/14 Awg Max With 1/18, Number Of Conductors: 2 to 5, Material: Flame-Retardant Polypropelene, Color: Yellow, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT4 |
| Weight per unit  | 1.7 (lbs/each)  |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                |                               |
|----------------|-------------------------------|
| Material       | Flame-retardant Polypropelene |
| Voltage Rating | 600                           |

### Material, Color, and Finish

|       |        |
|-------|--------|
| Color | Yellow |
|-------|--------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | WIRETWIST WIRE CONNECTOR, WT4 YELLOW, 500/BAG  |
| extra long description | IDEAL WT4-B WIRE-TWIST CONN.,YELLOW  |
| Features               | With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing |
| Long Description       | Buchanan, Wire Connector, WireTwist, Conductor Range: 18 - 10 AWG, 3/18 AWG Min, 4/14 AWG MAX With 1/18, Number Of Conductors: 2 to 5, Material: Flame-retardant Polypropelene, Color: Yellow, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT4  |
| Product Type           | Wire-Twist Conn., Yellow, Bag500   |
| Special Features       | 1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip;Model Number: WT4;Ribbed Cap Provides Positive Grip For Fast, Easy Installation;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F);UL 486C Listed And CSA 22.2 #188 Certified                      |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Buchanan       |
| GTIN                      | 00781789610078 |
| Manufacturers Part Number | WT4-B          |
| UPC                       | 781789610078   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
|----------------------|--|

## Availability

|             |     |
|-------------|-----|
| minimum qty | 500 |
|-------------|-----|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 10000 |
| Weight Per each | 1.7   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Insulating or Joining 1 or more conductors                       |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard                 | CSA C22.2 #188, UL 486C Listed, RoHS                             |