



WW-716

GENERAL Vinyl Electrical Tape

COLORS

- Brown
- Red
- Orange
- Yellow

- Green
- Blue
- Purple
- Gray
- White

SPECIFICATIONS

| | |
|-----------------------|--------------|
| Thickness | 7 mil |
| Adhesion to steel | 16 oz/in |
| Adhesion to backing | 16 oz/in |
| Tensile strength | 15 lb/in |
| Elongation | 200% |
| Operating temperature | 20°F - 176°F |
| Dielectric strength | 1200 V/mil |
| Certification | UL/CSA |

APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

KEY FEATURES

- Good adhesion and elasticity
- All weather performance
- Great tensile strength
- Resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 60'

COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



www.warriorwrap.com



NSi Industries, LLC
800.321.5847
www.nsiindustries.com



WW-716

GENERAL Vinyl Electrical Tape

COLORS

- Brown
- Red
- Orange
- Yellow

- Green
- Blue
- Purple
- Gray
- White

SPECIFICATIONS

| | |
|-----------------------|--------------|
| Thickness | 7 mil |
| Adhesion to steel | 16 oz/in |
| Adhesion to backing | 16 oz/in |
| Tensile strength | 15 lb/in |
| Elongation | 200% |
| Operating temperature | 20°F - 176°F |
| Dielectric strength | 1200 V/mil |
| Certification | UL/CSA |

APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

KEY FEATURES

- Good adhesion and elasticity
- All weather performance
- Great tensile strength
- Resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 60'

COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



www.warriorwrap.com



NSi Industries, LLC
800.321.5847
www.nsiindustries.com