



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WW716GN 3/4"X60' GRN GP Vny Tape

Nsi Industries

Catalog Number	WW716GN
Manufacturer	Nsi Industries
Description	Warriorwrap WW-716-GN Green Vinyl General Use Electrical Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 7MIL Thick, 60FT Long and Has A Max Temperature Rating Of 176 Degrees. The Strong Adhesion Helps Stick to Uneven Surfaces and Keeps The Backing In Place. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires.
Weight per unit	0.1900 (lbs/each)
Product Category	Markers & Marking Tapes

Features

adhesion strength	16
Material	Vinyl
maximum voltage	600
Temperature Range	20° - 176°
Tensile Strength	15
Warranty	1 YEAR

Material, Color, and Finish

Backing Material	Plasticized Polyvinyl Chloride (PVC)
Color	Green

Dimensions and Weight

Length	60
Size	Thickness - 7mil - Length-60' - Width 3/4"
Thickness	.007
Width	.750



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/4"X60' GRN GP VNY TAPE
extra long description	NSI WW-716-GN Vinyl Electrical Tape
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity to hold tight in indoor residential or commercial environments.
Long Description	WarriorWrap WW-716-GN Green Vinyl General Use Electrical Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 7mil thick, 60ft long and has a max temperature rating of 176 degrees. The strong adhesion helps stick to uneven surfaces and keeps the backing in place. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.
Product Type	Vinyl Electrical Tape 7MIL .75" 60FT GR
Special Features	Good Adhesion and Elasticity, All Weather Performance, Great Tensile Strength, Resistant To UV, Abrasion and Corrosion, Flame-Retardant.

Manufacturer Information

Brand	NSI
GTIN	00662381367419
Manufacturers Part Number	WW-716-GN
UPC	662381367419

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	GENERAL PURPOSE

Packaging

Carton	1
Weight Per each	0.19

Uses, Certifications, and Standards

Application	NSI
standard	UL 510