



WW-732

PREMIUM Vinyl Electrical Tape

COLORS

- Brown
- Red
- Orange
- Yellow
- Green
- Blue
- Purple
- Gray
- White

SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	33.3 oz/in
Adhesion to backing	33.2 oz/in
Tensile strength	19 lb/in
Elongation	285%
Operating temperature	0°F - 221°F
Dielectric strength	1289 V/mil
Certification	UL/CSA

APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

KEY FEATURES

- Superior adhesion and elasticity
- Extreme weather performance
- Excellent tensile strength
- Highly resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 66'

COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



www.warriorwrap.com



NSi Industries, LLC
800.321.5847
www.nsiindustries.com



WW-732

PREMIUM Vinyl Electrical Tape

COLORS

- Brown
- Red
- Orange
- Yellow

- Green
- Blue
- Purple
- Gray
- White

SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	33.3 oz/in
Adhesion to backing	33.2 oz/in
Tensile strength	19 lb/in
Elongation	285%
Operating temperature	0°F - 221°F
Dielectric strength	1289 V/mil
Certification	UL/CSA

APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

KEY FEATURES

- Superior adhesion and elasticity
- Extreme weather performance
- Excellent tensile strength
- Highly resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 66'

COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



www.warriorwrap.com



NSi Industries, LLC
800.321.5847
www.nsiindustries.com