



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WWCYC Yellow Winged Wire Connector 100/BK

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | WWCYC   |
| Manufacturer     | Nsi Industries  |
| Description      | Winged Wire Connector, (2) #18 Awg Conductor Size, (3) #12 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Yellow Insulation Color, +221 °F Operating Temperature, 0.717 In Overall Width, 1.016 In Overall Height, 600 V, 0.46 LB |
| Weight per unit  | 0.4600 (lbs/each)   |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                      |              |
|----------------------|--------------|
| Number of Conductors | 1            |
| Voltage Rating       | 600 V        |
| Warranty             | 1 YEAR       |
| Wire Type            | CU Wire Only |

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Finish | Thermoplastic |
|--------|---------------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | YELLOW WINGED WIRE CONNECTOR 100/BK |
| extra long description | NSI WWC-Y-C WW Semi-Conducting Tape |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00662381361806 |
| UPC  | 662381361806   |

### Taxonomies, Classifications, and Categories

|                      |           |
|----------------------|-----------|
| Category Description | WIRE NUTS |
|----------------------|-----------|

### Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 100  |
| Weight Per each | 0.46 |

### Uses, Certifications, and Standards

|                          |       |
|--------------------------|-------|
| environmental conditions | 105 C |
| Temperature Rating       | 105 C |