

Specifications



Eaton XBUT25BK

Eaton XB IEC terminal block, Screw connection single level-through-feed, Black, 12 AWG/2.5 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT25BK
UPC	786685231303
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.2 in
PRODUCT WEIGHT	0.02 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	32A (IEC), 22A (EN), 28A (EN), 20A (UL)
VOLTAGE RATING	IEC 800V, EN 700V, UL 600V

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XBUT25BK](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton XBUT25BK

Eaton XB IEC terminal block, Screw connection single level-through-feed, Black, 12 AWG/2.5 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT25BK
UPC	786685231303
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.2 in
PRODUCT WEIGHT	0.02 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	32A (IEC), 22A (EN), 28A (EN), 20A (UL)
VOLTAGE RATING	IEC 800V, EN 700V, UL 600V

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XBUT25BK](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

