

# Eaton XBUT35

Catalog Number: XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A



## General specifications

|                             |                             |
|-----------------------------|-----------------------------|
| <b>Product Name</b>         | <b>Catalog Number</b>       |
| Eaton XB IEC terminal block | XBUT35                      |
| <b>UPC</b>                  | <b>Product Length/Depth</b> |
| 782116905065                | 2.37 in                     |
| <b>Product Height</b>       | <b>Product Width</b>        |
| 2.88 in                     | 0.63 in                     |
| <b>Product Weight</b>       | <b>Warranty</b>             |
| 0.02 lb                     | 1 year                      |
| <b>Certifications</b>       |                             |
| CSA Certified               |                             |
| UL Listed                   |                             |

## Product specifications

### Type

IEC-XB Series

### Amperage Rating

527 (IEC), 40A (EN), 50A (EN), 50A (UL)

### Voltage rating

IEC 800V, EN 700V, UL 600V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT35](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)