



Powering Business Worldwide

pe.eaton.com

## Screw Connection Fuse Terminal Blocks

**XBUT4FBEL250**

**UPC:**782116905249

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

### Warranties:

- 1 year

### Specifications:

- **Special Features:** With LED 110–250V, 0.5–2.5 mA light
- **Type:** IEC-XB Series
- **Amperage Rating:** 6.30A (IEC), 6.30A (UL)
- **Voltage Rating:** UL 600V
- **Maximum Wire Size:** 10 AWG/4 mm<sup>2</sup>
- **Quantity:** 50
- **Used With:** 5 x 20 mm Fuse
- **Wire Size:** #26-10 AWG
- **Color:** Black

### Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT4FBEL250](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data







Powering Business Worldwide

pe.eaton.com

## Screw Connection Fuse Terminal Blocks

**XBUT4FBEL250**

**UPC:**782116905249

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

### Warranties:

- 1 year

### Specifications:

- **Special Features:** With LED 110–250V, 0.5–2.5 mA light
- **Type:** IEC-XB Series
- **Amperage Rating:** 6.30A (IEC), 6.30A (UL)
- **Voltage Rating:** UL 600V
- **Maximum Wire Size:** 10 AWG/4 mm<sup>2</sup>
- **Quantity:** 50
- **Used With:** 5 x 20 mm Fuse
- **Wire Size:** #26-10 AWG
- **Color:** Black

### Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT4FBEL250](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data



