

Specifications

Eaton XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm² maximum wire

Product specifications

TYPE	Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse
AMPERAGE RATING	10A (IEC), 10A (UL)
VOLTAGE RATING	UL 400V

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBNL24
UPC	782116905263
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.



Specifications

Eaton XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm² maximum wire

Product specifications

TYPE	Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse
AMPERAGE RATING	10A (IEC), 10A (UL)
VOLTAGE RATING	UL 400V

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBNL24
UPC	782116905263
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.

