



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## XC270 1/2" STR Squeeze Flex Conn

*Abb Installation Products, Inc*

|                  |  |
|------------------|--|
| Catalog Number   | XC270  |
| Manufacturer     | Abb Installation Products, Inc   |
| Description      | Connector, Straight Squeeze-Type, Size 1/2 Inch, Clamping Range 0.74 Inch - 0.92 Inch, Length 1.43 Inch, Die Cast Zinc |
| Weight per unit  | 0.0830 (lbs/each)  |
| Product Category | Liquid Tight Fittings  |

### Features

|          |               |
|----------|---------------|
| Material | Zinc Die Cast |
|----------|---------------|

### Dimensions and Weight

|      |          |
|------|----------|
| Size | 1/2 INCH |
|------|----------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 1/2" STR SQUEEZE FLEX CONN   |
| extra long description | ABB XC 270 1/2 INCH CONN,SQZ,AC/FLE  |
| Long Description       | Connector, Straight Squeeze-Type, Size 1/2 Inch, Clamping Range 0.74 Inch - 0.92 Inch, Length 1.43 Inch, Die Cast Zinc |
| Product Type           | 1/2 Inch Conn, SQZ, Ac/Flex, DC  |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Steel City     |
| GTIN                      | 00785991447040 |
| Manufacturers Part Number | XC 270         |
| UPC                       | 785991447040   |

### Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | FLEX & MC FITTINGS |
| Type                 | Squeeze Connectors |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 25    |
| Package         | 250   |
| Weight Per each | 0.083 |

### Uses, Certifications, and Standards

|          |          |
|----------|----------|
| standard | UL e1383 |
|----------|----------|