

Eaton XJG24 SA

Catalog Number: XJG24 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 3/4" trade size

General specifications



Product Name

Eaton Crouse-Hinds series XJG expansion coupling

Catalog Number

XJG24 SA

UPC

782274915760

Product Length/Depth

8.3 in

Product Height

3.4 in

Product Width

5.1 in

Product Weight

1 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Type

Expansion

Conduit type

Rigid/IMC

Trade size

3/4"

Conduit movement - max

4"

Material

Copper-free aluminum

Resources

Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

Installation instructions

[IF 343 - Type XJ Expansion Joints](#)

[IF 1508 - Assembly-Free XJG](#)

Specifications and datasheets

[Eaton Specification Sheet - XJG24 SA](#)

[Expansion and Deflection Couplings](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XJG24 SA

Catalog Number: XJG24 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 3/4" trade size

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series XJG expansion coupling	XJG24 SA
	UPC
	782274915760
Product Length/Depth	Product Height
8.3 in	3.4 in
Product Width	Product Weight
5.1 in	1 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Type

Expansion

Conduit type

Rigid/IMC

Trade size

3/4"

Conduit movement - max

4"

Material

Copper-free aluminum

Resources

Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

Installation instructions

[IF 343 - Type XJ Expansion Joints](#)

[IF 1508 - Assembly-Free XJG](#)

Specifications and datasheets

[Eaton Specification Sheet - XJG24 SA](#)

[Expansion and Deflection Couplings](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)