

Guarded Pilot Lights for Group B Applications

Class I, Groups B, C & D
Class II, Groups E, F & G
NEMA 3, 4, 7 & 9



XL Long Series
(Panel Mount)



XLS Short Series
(Surface Mount)



Replacement Cap

FEATURES

- Explosionproof pilot lights are suitable for panel or surface mount applications.
- Sealed construction and can be relamped from the front by removal of lens cap.
- Made with 3/4" NPSM threads.
- 8" flexible leads, other lengths on special order, or screw terminal (suffix T).
- All lens caps are black anodized aluminum finish.
- **Maximum installation thickness:** 1 13/16" on Long Series, 5/8" on Short Series.
- **Standard Series**-Equipped with candelabra base receptacles and 6 watt 120 volt 6S6 Clear 1500 hr. avg. lamps. Also available with 6, 12, 24, 30, 50, 75 and 135 volt lamps. Specify voltage desired.
- **Slide Base Series**-Equipped with slide base receptacles and 120 volt 5000 hr. avg. lamps with slide base. Also available with 6, 12, 24, 48 and 60 volt lamps. Specify voltage desired.

STANDARD SERIES

Panel Mount Cat #	Surface Mount Cat #	Description	Weight (lbs.)
XLA-GH	XLSA-GH	Amber Lens	1/2
XLB-GH	XLSB-GH	Blue Lens	1/2
XLC-GH	XLSC-GH	Clear Lens	1/2
XLG-GH	XLSG-GH	Green Lens	1/2
XLR-GH	XLSR-GH	Red Lens	1/2
XLW-GH	XLSW-GH	White Lens	1/2

SLIDE BASE SERIES

Panel Mount Cat #	Surface Mount Cat #	Description	Weight (lbs.)
XLAS-GH	XLSAS-GH	Amber Lens	1/2
XLBS-GH	XLSBS-GH	Blue Lens	1/2
XLCS-GH	XLSCS-GH	Clear Lens	1/2
XLGS-GH	XLSGS-GH	Green Lens	1/2
XLRS-GH	XLSRS-GH	Red Lens	1/2
XLWS-GH	XLSWS-GH	White Lens	1/2

*Add suffix T to P/N for screw terminal (Example: XLAST-GH)

REPLACEMENT CAP

Cat #	Description	Weight (lbs.)
XLA-GCH	Amber Lens	1/8
XLB-GCH	Blue Lens	1/8
XLC-GCH	Clear Lens	1/8
XLG-GCH	Green Lens	1/8
XLR-GCH	Red Lens	1/8
XLW-GCH	White Lens	1/8

Guarded Pilot Lights for Group B Applications



**XL Long Series
(Panel Mount)**



**XLS Short Series
(Surface Mount)**



Replacement Cap

**Class I, Groups B, C & D
Class II, Groups E, F & G
NEMA 3, 4, 7 & 9**

FEATURES

- Explosionproof pilot lights are suitable for panel or surface mount applications.
- Sealed construction and can be relamped from the front by removal of lens cap.
- Made with 3/4" NPSM threads.
- 8" flexible leads, other lengths on special order, or screw terminal (suffix T).
- All lens caps are black anodized aluminum finish.
- **Maximum installation thickness:** 1 13/16" on Long Series, 5/8" on Short Series.
- **Standard Series**-Equipped with candelabra base receptacles and 6 watt 120 volt 6S6 Clear 1500 hr. avg. lamps. Also available with 6, 12, 24, 30, 50, 75 and 135 volt lamps. Specify voltage desired.
- **Slide Base Series**-Equipped with slide base receptacles and 120 volt 5000 hr. avg. lamps with slide base. Also available with 6, 12, 24, 48 and 60 volt lamps. Specify voltage desired.

STANDARD SERIES

Panel Mount Cat #	Surface Mount Cat #	Description	Weight (lbs.)
XLA-GH	XLSA-GH	Amber Lens	1/2
XLB-GH	XLSB-GH	Blue Lens	1/2
XLC-GH	XLSC-GH	Clear Lens	1/2
XLG-GH	XLSG-GH	Green Lens	1/2
XLR-GH	XLSR-GH	Red Lens	1/2
XLW-GH	XLSW-GH	White Lens	1/2

SLIDE BASE SERIES

Panel Mount Cat #	Surface Mount Cat #	Description	Weight (lbs.)
XLAS-GH	XLSAS-GH	Amber Lens	1/2
XLBS-GH	XLSBS-GH	Blue Lens	1/2
XLCS-GH	XLSCS-GH	Clear Lens	1/2
XLGS-GH	XLSGS-GH	Green Lens	1/2
XLRS-GH	XLSRS-GH	Red Lens	1/2
XLWS-GH	XLSWS-GH	White Lens	1/2

*Add suffix T to P/N for screw terminal (Example: XLAST-GH)

REPLACEMENT CAP

Cat #	Description	Weight (lbs.)
XLA-GCH	Amber Lens	1/8
XLB-GCH	Blue Lens	1/8
XLC-GCH	Clear Lens	1/8
XLG-GCH	Green Lens	1/8
XLR-GCH	Red Lens	1/8
XLW-GCH	White Lens	1/8