

# Eaton XTAE032C10T032

Catalog Number: XTAE032C10T032

Eaton XT IEC electronic motor starter, Full voltage non-reversing IEC starter, 32 A, 24 V 50/60 Hz, 1NO, C frame, 45 mm, 24-32 A, Screw terminals



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC electronic motor starter	XTAE032C10T032
<b>UPC</b>	<b>Product Length/Depth</b>
782116864126	5.5 in
<b>Product Height</b>	<b>Product Width</b>
5.37 in	4.15 in
<b>Product Weight</b>	<b>Warranty</b>
2.35 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
RoHS Compliant	IEC 60947
ATEX Compliant	CSA Certified
	EN 60947
<b>Catalog Notes</b>	
Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)	

Amperage Rating

32A

Overload range

24-32 A

Type

Full voltage non-reversing IEC starter

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vac, 50/60 Hz

Contact configuration

1 NO

Frame

C

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - XTAE032C10T032](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton XTAE032C10T032

Catalog Number: XTAE032C10T032

Eaton XT IEC electronic motor starter, Full voltage non-reversing IEC starter, 32 A, 24 V 50/60 Hz, 1NO, C frame, 45 mm, 24-32 A, Screw terminals



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC electronic motor starter	XTAE032C10T032
<b>UPC</b>	<b>Product Length/Depth</b>
782116864126	5.5 in
<b>Product Height</b>	<b>Product Width</b>
5.37 in	4.15 in
<b>Product Weight</b>	<b>Warranty</b>
2.35 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
RoHS Compliant	IEC 60947
ATEX Compliant	CSA Certified
	EN 60947
<b>Catalog Notes</b>	
Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)	

**Amperage Rating**

32A

**Overload range**

24-32 A

**Type**

Full voltage non-reversing IEC starter

**Frame size**

45 mm

**Terminals**

Screw terminals

**Coil**

24 Vac, 50/60 Hz

**Contact configuration**

1 NO

**Frame**

C

**Catalogs**[Eaton's Volume 5—Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTAE032C10T032](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)