

Eaton XTAE032C10T032

Catalog Number: XTAE032C10T032

Eaton XT IEC electronic motor starter, Full voltage non-reversing IEC starter, 32 A, 24 V 50/60 Hz, 1NO, C frame, 45 mm, 24-32 A, Screw terminals



Photo is representative

General specifications

| | |
|--|-----------------------------|
| Product Name | Catalog Number |
| Eaton XT IEC electronic motor starter | XTAE032C10T032 |
| UPC | Product Length/Depth |
| 782116864126 | 5.5 in |
| Product Height | Product Width |
| 5.37 in | 4.15 in |
| Product Weight | Warranty |
| 2.35 lb | 1 year |
| Compliances | Certifications |
| CE Marked | UL Listed |
| RoHS Compliant | IEC 60947 |
| ATEX Compliant | CSA Certified |
| | EN 60947 |
| Catalog Notes | |
| Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A) | |

Amperage Rating

32A

Overload range

24-32 A

Type

Full voltage non-reversing IEC starter

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vac, 50/60 Hz

Contact configuration

1 NO

Frame

C

Catalogs[Eaton's Volume 5—Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTAE032C10T032](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia