

Eaton XTCE032C01C

Catalog Number: XTCE032C01C

Eaton XT IEC contactor, 32A, 412 Vac 50 Hz, 480 Vac 60 Hz, 1NC, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC contactor

UPC

782116485925

Product Height

3.898 in

Product Weight

0.9 lb

Compliances

RoHS Compliant

CE Marked

Catalog Number

XTCE032C01C

Product Length/Depth

3.425 in

Product Width

1.85 in

Warranty

1 year

Certifications

UL Listed

CSA Certified

EN 60947

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

32A

HP rating - max

3, 5, 5/ 10, 10, 20, 25 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

412-480 Vac, 50/60 Hz

Contact configuration

1 NC

Continuous ampere rating

32 A

Series

XT IEC

Operation

Non-reversing

Resources

Specifications and datasheets

Eaton Specification Sheet - XTCE032C01C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTCE032C01C

Catalog Number: XTCE032C01C

Eaton XT IEC contactor, 32A, 412 Vac 50 Hz, 480 Vac 60 Hz, 1NC, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC contactor

UPC

782116485925

Product Height

3.898 in

Product Weight

0.9 lb

Compliances

RoHS Compliant

CE Marked

Catalog Number

XTCE032C01C

Product Length/Depth

3.425 in

Product Width

1.85 in

Warranty

1 year

Certifications

UL Listed

CSA Certified

EN 60947

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

32A

HP rating - max

3, 5, 5/ 10, 10, 20, 25 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

412-480 Vac, 50/60 Hz

Contact configuration

1 NC

Continuous ampere rating

32 A

Series

XT IEC

Operation

Non-reversing

Resources

Specifications and datasheets

Eaton Specification Sheet - XTCE032C01C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)