

Eaton XTCE032C10H

Catalog Number: XTCE032C10H

Eaton XT IEC contactor, 32A, 240 Vac, 50 Hz, 277V 60 Hz, 1NO, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC contactor

Catalog Number

XTCE032C10H

UPC

782116486144

Product Length/Depth

3.425 in

Product Height

3.898 in

Product Width

1.85 in

Product Weight

0.9 lb

Warranty

1 year

Compliances

RoHS Compliant

CE Marked

Certifications

IEC 60947

CSA Certified

EN 60947

UL Listed

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

32A

HP rating - max

3, 5, 5/ 10, 10, 20, 25 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

240-277 Vac, 50/60 Hz

Contact configuration

1 NO

Continuous ampere rating

32 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_C 3D Model Xchange](#)

[XTCE_C AutoCAD 2D Footprint](#)

[XTCE_C 2D Drawing Xchange](#)

[XTCE_C 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCE032C10H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)