

# Specifications



Photo is representative

## Eaton XTCE065D00C

Eaton XT IEC contactor, 65A, 415 Vac, 50 Hz, 480 Vac, 60 Hz, 0NO-0NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE065D00C
<b>UPC</b>	782116486601
<b>PRODUCT LENGTH/DEPTH</b>	2.244 in
<b>PRODUCT HEIGHT</b>	5.945 in
<b>PRODUCT WIDTH</b>	4.567 in
<b>PRODUCT WEIGHT</b>	2.4 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	UL Listed CSA Certified IEC 60947 EN 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



### Product specifications

**AMPERAGE RATING** 65A

### Resources

<b>HP RATING - MAX</b>	5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @ 115,200,230/200,230,460,575 V)
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Full voltage non-reversing contactor
<b>FREQUENCY RATING</b>	50-60 Hz
<b>FRAME SIZE</b>	55 mm
<b>TERMINALS</b>	Screw terminals
<b>COIL</b>	412-480 Vac, 50/60 Hz
<b>COIL VOLTAGE</b>	415-480 Vac, 50/60 Hz
<b>CONTACT CONFIGURATION</b>	0 NO, 0 NC
<b>CONTINUOUS AMPERE RATING</b>	65 A
<b>SERIES</b>	XT IEC
<b>OPERATION</b>	Non-reversing

**SPECIFICATIONS AND  
DATASHEETS**

[Eaton Specification Sheet -  
XTCE065D00C](#)

**WARRANTY GUIDES**

[Selling Policy 25-000 -  
Distribution and Control  
Products and Services](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest  
product and support information.

All other trademarks are property of  
their respective owners.

