

Eaton XTCR009B21TD

Catalog Number: XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC contactor

UPC

782116884896

Product Height

68 mm

Product Weight

0.28 kg

Compliances

CE Marked

RoHS Compliant

Catalog Number

XTCR009B21TD

Product Length/Depth

117 mm

Product Width

90 mm

Warranty

1 year

Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

9A

HP rating - max

0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

24 Vdc

Contact configuration

2 NO, 2 NO

Continuous ampere rating

9 A

Series

XT IEC

Operation

Reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCR009B21TD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTCR009B21TD

Catalog Number: XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC contactor

UPC

782116884896

Product Height

68 mm

Product Weight

0.28 kg

Compliances

CE Marked

RoHS Compliant

Catalog Number

XTCR009B21TD

Product Length/Depth

117 mm

Product Width

90 mm

Warranty

1 year

Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

9A

HP rating - max

0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

24 Vdc

Contact configuration

2 NO, 2 NO

Continuous ampere rating

9 A

Series

XT IEC

Operation

Reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCR009B21TD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)