

# Specifications

## Eaton XTCR009B21TD



Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCR009B21TD
<b>UPC</b>	782116884896
<b>PRODUCT LENGTH/DEPTH</b>	117 mm
<b>PRODUCT HEIGHT</b>	68 mm
<b>PRODUCT WIDTH</b>	90 mm
<b>PRODUCT WEIGHT</b>	0.28 kg
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified EN 60947 UL Listed IEC 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	9A
HP RATING - MAX	0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	24 Vdc
CONTACT CONFIGURATION	2 NO, 2 NO
CONTINUOUS AMPERE RATING	9 A
SERIES	XT IEC
OPERATION	Reversing

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR009B21TD](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton XTCR009B21TD



Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCR009B21TD
<b>UPC</b>	782116884896
<b>PRODUCT LENGTH/DEPTH</b>	117 mm
<b>PRODUCT HEIGHT</b>	68 mm
<b>PRODUCT WIDTH</b>	90 mm
<b>PRODUCT WEIGHT</b>	0.28 kg
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified EN 60947 UL Listed IEC 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	9A
HP RATING - MAX	0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	24 Vdc
CONTACT CONFIGURATION	2 NO, 2 NO
CONTINUOUS AMPERE RATING	9 A
SERIES	XT IEC
OPERATION	Reversing

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR009B21TD](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

