

Specifications

Eaton XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor



Photo is representative



General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR009B21TD
UPC	782116884896
PRODUCT LENGTH/DEPTH	117 mm
PRODUCT HEIGHT	68 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.28 kg
WARRANTY	1 year
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified EN 60947 UL Listed IEC 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

AMPERAGE RATING	9A
HP RATING - MAX	0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	24 Vdc
CONTACT CONFIGURATION	2 NO, 2 NO
CONTINUOUS AMPERE RATING	9 A
SERIES	XT IEC
OPERATION	Reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR009B21TD](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor



Photo is representative



General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR009B21TD
UPC	782116884896
PRODUCT LENGTH/DEPTH	117 mm
PRODUCT HEIGHT	68 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.28 kg
WARRANTY	1 year
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified EN 60947 UL Listed IEC 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

AMPERAGE RATING	9A
HP RATING - MAX	0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	24 Vdc
CONTACT CONFIGURATION	2 NO, 2 NO
CONTINUOUS AMPERE RATING	9 A
SERIES	XT IEC
OPERATION	Reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR009B21TD](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

