

Specifications

Eaton XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor



Photo is representative



General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR009B21TD
UPC	782116884896
PRODUCT LENGTH/DEPTH	117 mm
PRODUCT HEIGHT	68 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.28 kg
WARRANTY	1 year
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified EN 60947 UL Listed IEC 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

Product specifications

AMPERAGE RATING	9A
HP RATING - MAX	0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	24 Vdc
CONTACT CONFIGURATION	2 NO, 2 NO
CONTINUOUS AMPERE RATING	9 A
SERIES	XT IEC
OPERATION	Reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR009B21TD](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

