

Eaton XTCR025C21A

Catalog Number: XTCR025C21A

Eaton XT IEC contactor, 25A, 110 Vac 50 Hz, 120 Vac 60 Hz, 2NO-2NO, 25A, Frame C, 45 mm, 50-60 Hz, 2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, , Screw terminals, FVR

General specifications



Product Name
Eaton XT IEC contactor

Catalog Number
XTCR025C21A

UPC
786685180236

Product Length/Depth
7.5 in

Product Height
4.5 in

Product Width
4.75 in

Product Weight
2.45 lb

Certifications
UL Listed

defaultTaxonomyAttributeLabel

Amperage Rating

25A

HP rating - max

2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frequency rating

50-60 Hz

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

2 NO, 2 NO

Continuous ampere rating

25 A

Series

XT IEC

Operation

Reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCR_C 3D Inventor](#)

[XTCR_C AutoCAD 2D Footprint](#)

[XTCR_C 3D Model Xchange](#)

[XTCR_C 2D PDF](#)

[XTCR_C AutoCAD 2D Footprint \(mm\)](#)

[XTCR_C 2D Drawing Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCR025C21A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTCR025C21A

Catalog Number: XTCR025C21A

Eaton XT IEC contactor, 25A, 110 Vac 50 Hz, 120 Vac 60 Hz, 2NO-2NO, 25A, Frame C, 45 mm, 50-60 Hz, 2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, , Screw terminals, FVR

General specifications



Product Name
Eaton XT IEC contactor

Catalog Number
XTCR025C21A

UPC
786685180236

Product Length/Depth
7.5 in

Product Height
4.5 in

Product Width
4.75 in

Product Weight
2.45 lb

Certifications
UL Listed

defaultTaxonomyAttributeLabel

Amperage Rating

25A

HP rating - max

2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frequency rating

50-60 Hz

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

2 NO, 2 NO

Continuous ampere rating

25 A

Series

XT IEC

Operation

Reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCR_C 3D Inventor](#)

[XTCR_C AutoCAD 2D Footprint](#)

[XTCR_C 3D Model Xchange](#)

[XTCR_C 2D PDF](#)

[XTCR_C AutoCAD 2D Footprint \(mm\)](#)

[XTCR_C 2D Drawing Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCR025C21A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)