

Eaton XTCR032C21TD

Catalog Number: XTCR032C21TD

Eaton XT IEC contactor, 32A, 24-27 Vdc, 2NO-2NO, 32A, Frame C, 45 mm, 3, 5/ 10, 10, 20, 25 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCR032C21TD

UPC

782116885695

Product Length/Depth

4.75 in

Product Height

4.5 in

Product Width

7.5 in

Product Weight

2.45 lb

Warranty

1 year

Compliances

CE Marked

RoHS Compliant

Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

32A

HP rating - max

3, 5/ 10, 10, 20, 25 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vdc

Coil voltage

24-27 Vdc

Contact configuration

2 NO, 2 NO

Continuous ampere rating

32 A

Series

XT IEC

Operation

Reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCR_C 3D Inventor](#)

[XTCR_C 2D Drawing Xchange](#)

[XTCR_C 2D PDF](#)

[XTCR_C AutoCAD 2D Footprint \(mm\)](#)

[XTCR_C AutoCAD 2D Footprint](#)

[XTCR_C 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCR032C21TD](#)

Eaton XTCR032C21TD

Catalog Number: XTCR032C21TD

Eaton XT IEC contactor, 32A, 24-27 Vdc, 2NO-2NO, 32A, Frame C, 45 mm, 3, 5/ 10, 10, 20, 25 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

UPC

782116885695

Product Height

4.5 in

Product Weight

2.45 lb

Compliances

CE Marked

RoHS Compliant

Catalog Number

XTCR032C21TD

Product Length/Depth

4.75 in

Product Width

7.5 in

Warranty

1 year

Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

32A

HP rating - max

3, 5/ 10, 10, 20, 25 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil

24 Vdc

Coil voltage

24-27 Vdc

Contact configuration

2 NO, 2 NO

Continuous ampere rating

32 A

Series

XT IEC

Operation

Reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCR_C 3D Inventor](#)

[XTCR_C 2D Drawing Xchange](#)

[XTCR_C 2D PDF](#)

[XTCR_C AutoCAD 2D Footprint \(mm\)](#)

[XTCR_C AutoCAD 2D Footprint](#)

[XTCR_C 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCR032C21TD](#)