

Eaton XTCR080F11A

Catalog Number: XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR



General specifications

Product Name

Eaton XT IEC contactor

UPC

782116356126

Product Height

6 in

Product Weight

4.7 lb

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947

Catalog Number

XTCR080F11A

Product Length/Depth

9.5 in

Product Width

6.5 in

Compliances

CE Marked
RoHS Compliant

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

80A

HP rating - max

7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frequency rating

50-60 Hz

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

80 A

Series

XT IEC

Operation

Reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCR080F11A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTCR080F11A

Catalog Number: XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR



General specifications

Product Name

Eaton XT IEC contactor

UPC

782116356126

Product Height

6 in

Product Weight

4.7 lb

Certifications

UL Listed
CSA Certified
IEC 60947
EN 60947

Catalog Number

XTCR080F11A

Product Length/Depth

9.5 in

Product Width

6.5 in

Compliances

CE Marked
RoHS Compliant

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

Amperage Rating

80A

HP rating - max

7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frequency rating

50-60 Hz

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

80 A

Series

XT IEC

Operation

Reversing

Resources

Specifications and datasheets

[Eaton Specification Sheet - XTCR080F11A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)