

Specifications



Eaton XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR080F11A
UPC	782116356126
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	6.5 in
PRODUCT WEIGHT	4.7 lb
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified IEC 60947 EN 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

Product specifications

AMPERAGE RATING	80A
HP RATING - MAX	7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FREQUENCY RATING	50-60 Hz
TERMINALS	Screw terminals
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	80 A
SERIES	XT IEC
OPERATION	Reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR080F11A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR080F11A
UPC	782116356126
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	6.5 in
PRODUCT WEIGHT	4.7 lb
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified IEC 60947 EN 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

Product specifications

AMPERAGE RATING	80A
HP RATING - MAX	7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FREQUENCY RATING	50-60 Hz
TERMINALS	Screw terminals
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	80 A
SERIES	XT IEC
OPERATION	Reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR080F11A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

