



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA262N 2/0 Cu 2H Long 1/2 Burndy LLC

Catalog Number	YA262N
Manufacturer	Burndy LLC
Description	2/0 Awg Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Black Color Code, 13 Die Index.
Weight per unit	0.1400 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	13
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	BLACK
------------	-------

### Descriptions

Description	2/0 CU 2H LONG 1/2
extra long description	BUR YA262N 2/0 CU 2-HOLE LONG 1/2
Long Description	2/0 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Black Color Code, 13 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 13, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Wire Strip Length: 1-9/16 IN, Finish: Electro-Tin Plated, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W26VT, W26RT, X26RT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W26VT, W26RT, X26RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U26RT Die, (2), Y46 Tool, U26RT Die With PUADP-1 Adapter, (2), Color Code: Black

### Manufacturer Information

Brand	BURNDY
GTIN	00781810502808
Manufacturers Part Number	YA262N
UPC	781810502808

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.14

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B