



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA282N 4/0 Cu 2H Long 1/2 Burndy LLC

Catalog Number	YA282N
Manufacturer	Burndy LLC
Description	4/0 Awg Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Purple Color Code, 15 Die Index.
Weight per unit	0.2100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	15
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	PURPLE
------------	--------

Descriptions

Description	4/0 CU 2H LONG 1/2
extra long description	BUR YA282N 4/0 CU 2-HOLE LONG 1/2
Long Description	4/0 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Purple Color Code, 15 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Die Index: 15, Wire Strip Length: 1-11/16 IN, Tongue Angle: Straight, Finish: Electro-Tin Plated, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W28VT, W28RT Die, (4), X28RT Die, (6), Hydraulic: BCT500HS, Y500CTHS Tool, W28VT, W28RT Die, (4), X28RT Die, (6), Y35, Y39, Y750, PAT750 Tool, U28RT Die, (2), Y46 Tool, U28RT Die With PUADP-1 Adapter, (2)

Manufacturer Information

Brand	BURNDY
GTIN	00781810503652
Manufacturers Part Number	YA282N
UPC	781810503652

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Weight Per each	0.21

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B