



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA292LN 250MCM Cop 2H Lug

Burndy LLC

Catalog Number	YA292LN
Manufacturer	Burndy LLC
Description	250 Kcmil Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Yellow Color Code, 16 Die Index.
Weight per unit	0.2200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	16
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	YELLOW
------------	--------

Descriptions

Description	250MCM COP 2H LUG
extra long description	BUR YA292LN 250 CU 2-HOLE SHORT NEM
Long Description	250 kcmil CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Yellow Color Code, 16 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 1-1/8 IN, Tongue Angle: Straight, Die Index: 16, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W29VT Die, (2), X29RT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W29VT, W29RT Die, (2), X29RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U29RT Die, (1), Y46 Tool, U29RT Die With PUADP-1 Adapter, (1), Color C

Manufacturer Information

Brand	BURNDY
GTIN	00781810504222
Manufacturers Part Number	YA292LN
UPC	781810504222

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.22

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B