



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA2C2N 2AWG Cop 2H Lug Burndy LLC

Catalog Number	YA2C2N
Manufacturer	Burndy LLC
Description	2 Awg Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Brown Color Code, 10 Die Index.
Weight per unit	0.1000 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	10
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	BROWN
------------	-------

### Descriptions

Description	2AWG COP 2H LUG
extra long description	BUR YA2C2N 2STR CU 2-HOLE LONG NEMA
Long Description	2 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Brown Color Code, 10 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Die Index: 10, Tongue Angle: Straight, Wire Strip Length: 1-5/16 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W2CVT, W2CRT, X2CRT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W2CVT, W2CRT, X2CRT Die, (2), Y35, Y39, Y750, PAT750 Tool, U2CRT Die, (2), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (2), Color Code: Brown

### Manufacturer Information

Brand	BURNDY
GTIN	00781810500866
Manufacturers Part Number	YA2C2N
UPC	781810500866

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	25
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B