



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA31L11 350MCM 1H Lug *Burndy LLC*

Catalog Number	YA31L11
Manufacturer	Burndy LLC
Description	350 Kcmil Cu, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Red Color Code, 18 or 324 Die Index.
Weight per unit	0.1700 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	18
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	RED
------------	-----

### Descriptions

Description	350MCM 1H LUG
extra long description	BUR YA31L11 350 CU 1-HOLE SHORT 3/8
Long Description	350 kcmil CU, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, RED Color Code, 18 or 324 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight, Wire Strip Length: 1-3/16 IN, Temperature Rating: 90 DEG C, Die Index: 18, Finish: Electro-Tin Plated, Color Code: Red, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W31VT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W31VT, W31RT Die, (2), Y35, Y39, Y750, PAT750 Tool, U31RT, U29ART Die, (2), Y46 Tool, U31RT, U29ART Die With PUADP-1 Adapter, (2), Diele

### Manufacturer Information

Brand	BURNDY
GTIN	00781810018040
Manufacturers Part Number	YA31L11
UPC	781810018040

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.17

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B