



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA342N 500 Cu 2H Long 1/2 *Burndy LLC*

Catalog Number	YA342N
Manufacturer	Burndy LLC
Description	500 Kcmil Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Brown Color Code, 20 or 299 Die Index.
Weight per unit	0.6300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	20
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	BROWN
------------	-------

### Descriptions

Description	500 CU 2H LONG 1/2
extra long description	BUR YA342N 500 CU 2-HOLE LONG 1/2
Long Description	500 kcmil CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Brown Color Code, 20 or 299 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight, Die Index: 20, Temperature Rating: 90 DEG C, Wire Strip Length: 2-1/2 IN, Finish: Electro-Tin Plated, Color Code: Brown, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W34VT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W34VT, W34RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U34RT, U31ART Die, (4), Y46 Tool, U34RT, U31ART Die With PUADP-1 Adapter, (4), Cond

### Manufacturer Information

Brand	BURNDY
GTIN	00781810506059
Manufacturers Part Number	YA342N
UPC	781810506059

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	6
Weight Per each	0.63

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B