



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA392N 750 Cu 2H Long Nema *Burndy LLC*

Catalog Number	YA392N
Manufacturer	Burndy LLC
Description	Copper Compression Lug, 2 Hole W/O Inspection Window, 750 Kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel, Tin Plated.
Weight per unit	1.1 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	24
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	BLACK
------------	-------

Descriptions

Description	750 CU 2H LONG NEMA
extra long description	BUR YA392N 750 CU 2-HOLE LONG NEMA
Long Description	Copper Compression Lug, 2 Hole w/o Inspection Window, 750 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel, Tin Plated.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 24, Wire Strip Length: 2-3/4 IN, Finish: Electro-Tin Plated, Tongue Angle: Straight, Temperature Rating: 90 DEG C, Color Code: Black, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y35, Y39, Y750, PAT750 Tool, U39RT, P39RT Die, (4), Y46 Tool, U39RT Die With PUADP-1 Adapter, (4), Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (4), Conductor Type: Comme

Manufacturer Information

Brand	BURNDY
GTIN	00781810522356
Manufacturers Part Number	YA392N
UPC	781810522356

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	1.143

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B