



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS25 1/0AWG Butt Splice Long

Burndy LLC

Catalog Number	YS25
Manufacturer	Burndy LLC
Description	1/0 Awg Cu, Long Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Pink Color Code, 12 or 348 Die Index
Weight per unit	0.0800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	12
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	PINK
Finish	Tin-Plated

Descriptions

Description	1/0AWG BUTT SPLICE LONG
extra long description	BUR YS25 BUTT SPLICE LONG 1/0
Long Description	1/0 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, PINK Color Code, 12 or 348 Die Index
Product Type	Splice
Special Features	Features: UL Listed 90 DEG C, 600 Volts to 35 kV, Long Barrel Length: Ideal For 600 Volt Heavy Duty Applications, Also May Be Used At Higher Voltages Up To 35KV, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Much Greater Mechanical And Electrical Properties, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Oil Stop: No, Color Code: Pink, Tapered End: No, Die Index: 12 Or 348, Conducto

Manufacturer Information

Brand	BURNDY
GTIN	00781810507506
Manufacturers Part Number	YS25
UPC	781810507506

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS, Long Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B