



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YS25LBOX 1/0AWG Butt Splice

Burndy LLC

Catalog Number	YS25LBOX
Manufacturer	Burndy LLC
Description	1/0 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Pink Color Code, 12 or 348 Die Index.
Weight per unit	0.0500 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	12
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	PINK
Finish	Tin-Plated

### Descriptions

Description	1/0AWG BUTT SPLICE
extra long description	BUR YS25LBOX 1/0 STR. CU. BUTT SPLI
Long Description	1/0 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, PINK Color Code, 12 or 348 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length: Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, Oil Stop: No, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Color Code: Pink, Tapered End: No, Die Index: 12 Or 348, Conductor Type: Commercial Stranded Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R Tool, W25VT Die, (2), MD6,

### Manufacturer Information

Brand	BURNDY
GTIN	00781810556009
Manufacturers Part Number	YS25LBOX
UPC	781810556009

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.05

## Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B