



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS27LBOX 3/0AWG Butt Splice

Burndy LLC

Catalog Number	YS27LBOX
Manufacturer	Burndy LLC
Description	3/0 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Orange Color Code, 14 Die Index.
Weight per unit	0.0700 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	14
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	ORANGE
Finish	Tin-Plated

Descriptions

Description	3/0AWG BUTT SPLICE
extra long description	BUR YS27LBOX 3/0 STR. CU. BUTT SPLI
Long Description	3/0 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, ORANGE Color Code, 14 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length: Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, Oil Stop: No, Tapered End: No, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Color Code: Orange, Die Index: 14 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R Tool, W27VT Die, (2), MD6, OUR840 Tool, X27RT Die, (2), Y35, Y39,

Manufacturer Information

Brand	BURNDY
GTIN	00781810556504
Manufacturers Part Number	YS27LBOX
UPC	781810556504

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.07

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B