



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS2CLBOX 2AWG Butt Splice

Burndy LLC

Catalog Number	YS2CLBOX
Manufacturer	Burndy LLC
Description	2 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Brown Color Code, 10 Die Index
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	10
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	BROWN
Finish	Tin-Plated

Descriptions

Description	2AWG BUTT SPLICE
extra long description	BUR YS2CLBOX 2 STR. CU. BUTT SPLICE
Long Description	2 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, BROWN Color Code, 10 Die Index
Product Type	Splice
Special Features	Features: Standard Barrel Length: Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Oil Stop: No, Color Code: Brown, Tapered End: No, Die Index: 10 Element A, Conductor Type: Commercial Stranded Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y1MRTC Tool, (2), Y2MR Tool, M

Manufacturer Information

Brand	BURNDY
GTIN	00781810555255
Manufacturers Part Number	YS2CLBOX
UPC	781810555255

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B